

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.com

Email USA: techserv@sial.com


Outside USA: eurtechserv@sial.com

Product Specification

Product Name:
N-Butyldeoxynojirimycin - film (dried in situ)

Product Number: **B8299**
CAS Number: 72599-27-0

Formula: C₁₀H₂₂NO₄
Formula Weight: 219.28 AMU



TEST

Specification

Appearance (Form)	Powder
Appearance (Colour)	White
Solubility (Solvent)	Water
Solubility (Conc)	9.80 - 10.20 mg/ml
Solubility (Turbidity)	Clear
Solubility (Color)	Colorless
Elemental Anal. (%C anhydrous)	54.02 - 55.02 %
Elemental Anal. (%N anhydrous)	5.86 - 6.86 %
Purity (TLC)	≥ 98.00 %
NMR (Solvent)	D ₂ O
Identity by NMR	Consistent
Recommended Retest Period	-----
2 Years	

Specification: PRE.0.ZQ5.10000005928

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.