

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:  
Bois de roseProduct Number: **W215600**  
CAS Number: 8015-77-8  
MDL: MFCD00239823

TEST	Specification
Appearance (Color)	Colorless to Pale Yellow
Appearance (Form)	Liquid
Refractive index at 20 ° C	1.462 - 1.470
Infrared spectrum	Conforms to Structure
Distillation Range	195 - 205 °C
Specific Rotation	-4.0 - 6.0 °
Assay	75.00 - 92.00 %
Calculated as Linalool	
Specific Gravity	0.868 - 0.889
Solubility (Turbidity)	Pass
Dissolves in 1ml/6ml 60% Ethanol	
Arsenic (As)	≤ 3 ppm
Cadmium (Cd)	≤ 1 ppm
Mercury (Hg)	≤ 1 ppm
Lead (Pb)	≤ 10 ppm
Expiration Date Period	-----
5 Years	

Specification: PRD.1.ZQ5.10000018064

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.