


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:
Oxybutynin chloride - ≥98% (TLC), powder

Product Number: O2881
CAS Number: 1508-65-2
MDL: MFCD00072150
Formula: C₂₂H₃₁NO₃ · HCl
Formula Weight: 393.95 g/mol



TEST	Specification
Appearance (Color)	White
Appearance (Form)	Powder
Solubility (Color)	Colorless
Solubility (Turbidity) 50 mg/ml, H ₂ O	Clear
Loss on Drying	≤ 3.0 %
TLC PURITY	≥ 98 %
Titration with NaOH (Dried basis)	99.0 - 102.0 %

Specification: PRD.1.ZQ5.10000058181

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.