

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaldrich.com](http://www.sigmaldrich.com)


Email USA: [techserv@sial.com](mailto:techserv@sial.com)

Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:  
4-(Dimethylamino)pyridine - ReagentPlus®, ≥99%

**Product Number:** 107700  
**CAS Number:** 1122-58-3  
**MDL:** MFCD00006418  
**Formula:** C7H10N2  
**Formula Weight:** 122.17 g/mol



### TEST

### Specification

Appearance (Color)	White to Off-White
Appearance (Form)	Conforms to Requirements
Crystalline Powder, Crystalline Flakes, Chips or Granular Powder	
Infrared spectrum	Conforms to Structure
Purity (Titration by HCL04)	99.0 - 101.0 %
Purity (HPLC)	≥ 99.0 %
Solubility (Turbidity)	Clear to Very Slightly Hazy
Solubility Concentration: 50mg/ml, H2O	
Solubility (Color)	Colorless to Very Faint Yellow
Recommended Retest Period	-----
3 Years	

Specification: PRD.1.ZQ5.10000019641

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.