


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:
Tetrabutylammonium bromide - ACS reagent, ≥98.0%

Product Number: 426288
CAS Number: 1643-19-2
MDL: MFCD00011633
Formula: C₁₆H₃₆BrN
Formula Weight: 322.37 g/mol



TEST	Specification
Appearance (Color)	White
Appearance (Form) Crystals or Crystalline Powder	Conforms to Requirements
Infrared spectrum	Conforms to Structure
Titration by AgNO ₃	≥ 98.0 %
Impurity Tributylamine	≤ 0.5 %
Impurity Tributylamine Hydrobromide	≤ 0.5 %
Meets ACS Requirements	Current ACS Specification

Specification: PRD.2.ZQ5.10000021769

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.