

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:

Fibronectin Fragment III₁-C human - recombinant, expressed in E. coli, lyophilized powder, ≥90% (SDS-PAGE)

Product Number:

F3542

Storage Temperature:

-20 °C

TEST**Specification**

Appearance (Form)	Lyophilized Powder
Appearance (Colour)	White
Solubility (Solvent)	TBS
Solubility (Conc)	1.00 - 1.10 mg/ml
Solubility (Turbidity)	Clear
Solubility (Color)	Colorless
Gel Electroph. (Gel)	SDS-Page
Gel Electroph. (Stain)	Coomassie
Gel Electroph. (Description)	1 Major Band
Gel Elec. (Maj. Band at kDa)	8 - 15 kDa
Gel Electroph. (Purity)	≥ 90.0 %
Vial Content (Size)	0.500 - 0.500
Vial Content (Unit Of Measure)	mg Protein
Vial Content (Actual Content)	≥ 0.500
Vial Content (Overpack)	1.00 - 30.00 %
Vial Content (Testing Method)	Lowry
Microbial Contamination	Pass
Recommended Retest Period	-----
3 Years	

Specification: PRE.4.ZQ5.10000001669

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.