

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:

Poly(pyromellitic dianhydride-co-4,4'-oxydianiline), amic acid solution - 15.0 wt. %±5 wt. % in NMP/aromatic hydrocarbons (80%/20% solvent ratio)

Product Number:


575828

CAS Number:

25038-81-7

MDL:

MFCD00217729



Storage Temperature:

-20 °C

TEST**Specification**

Appearance (Color)

Colorless to Yellow to Red

Appearance (Form)

Liquid

Infrared spectrum

Conforms to Structure

Viscosity (Poise)

50.0 - 70.0

Solid Content

14.5 - 15.5 %

Specification: PRD.1.ZQ5.10000019924

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.