


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaldrich.com](http://www.sigmaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:  
Diphenyl ether - ≥99%, FG

**Product Number:** W366706  
**CAS Number:** 101-84-8  
**MDL:** MFCD00003034  
**Formula:** C<sub>12</sub>H<sub>10</sub>O  
**Formula Weight:** 170.21 g/mol



TEST	Specification
Appearance (Color)	White or Colorless
Appearance (Form)	Solid or Liquid
Proton NMR Spectrum	Conforms to Structure
Purity (GC)	≥ 99.0 %
Arsenic (As)	≤ 3 ppm
Cadmium (Cd)	≤ 1 ppm
Mercury (Hg)	≤ 1 ppm
Lead (Pb)	≤ 10 ppm
Expiration Date Period 5 Years	-----

Specification: PRD.2.ZQ5.10000036995

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.