

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:

Monoclonal Anti-Rabbit Immunoglobulins–Alkaline Phosphatase antibody produced in mouse – clone RG-16, purified immunoglobulin, buffered aqueous glycerol solution

Product Number:

**A2306****TEST****Specification**

Appearance (Form)	Liquid
Appearance (Turbidity)	Clear to Slightly Hazy
Appearance (Color)	Almost Colorless to Light Yellow
IgG Concentration (OD 280nm)	0.8 - 2.5 mg/ml
ELISA - Titer	1:40,000-1:50,000
WB-Cell Line/Tissue Extract	Hela Cells
WB Titer	1:160,000-1:320,000
IHC - Tissue	Human Tonsil
IHC - Fixation	FFPE-Formalin Fixed Paraffin Embedded
IHC - Titer	1:160-1:320
Recommended Retest Period	-----
2 Years	

Specification: PRE.0.ZQ5.10000016418

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.