

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:

Peptidyl Arginine Deiminase from rabbit skeletal muscle - buffered aqueous glycerol solution, ≥ 200 units/mg protein (Bradford)

Product Number:

P1584

Storage Temperature:

-70 °C

TEST**Specification**

Appearance (Form) Clear Solution	Conforms
Appearance (Colour)	Colorless
Protein Content (Method)	Bradford
Enzym. Assay (Spec. Activity)	≥ 200.00 U/mgP
Gel Electroph. (Gel)	SDS-Page
Gel Electroph. (Stain)	Coomassie
Gel Electroph. (Description)	1 Major Band
Vial Content (Size)	25 - 25
Vial Content (Unit Of Measure)	Units
Vial Content (Testing Method)	Enzymatic Assay
Vial Content (Overpack)	5.00 - 30.00 %
Recommended Retest Period 2 Years	-----

Specification: PRE.2.ZQ5.10000001473

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.