

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.com

Email USA: techserv@sial.com

Outside USA: eurtechserv@sial.com


Product Specification

Product Name:
Poly(OEGMA) - hydrazide functionalized, 25 wt% solution in water

Product Number: **901776**

Formula: $[\text{CH}_2\text{CCH}_3(\text{COO}(\text{CH}_2\text{CH}_2\text{O})_8\text{CH}_3)]_m$

Storage Temperature: 2 - 8 °C



TEST	Specification
Appearance (Color)	Colorless to Faint Yellow
Appearance (Form)	Liquid
Infrared Spectrum	Conforms to Structure
¹ H NMR Spectrum	Conforms to Structure
Residue on Evaporation	20 - 30 % wt
Molecular Weight by GPC	
Specification: Report Only	
Functionalization	
Hydrazide	
Specification: Report Only	
Recommended Retest Period	-----
1 Year	

Specification: PRD.0.ZQ5.10000102047

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.