

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaldrich.com](http://www.sigmaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:

Superfibronectin from human plasma – solution, sterile-filtered, BioReagent, suitable for cell culture

Product Number:

S5171

Storage Temperature:

2 - 8 °C

| TEST                                 | Specification  |
|--------------------------------------|----------------|
| Appearance (Form)<br>Clear Solution  | Conforms       |
| Appearance (Colour)                  | Colorless      |
| Protein Content (Method)             | Lowry          |
| Prot. Content (mg Protein/ml)        | 1.60 - 2.40    |
| Vial Content (Size)                  | 0.500 - 0.500  |
| Vial Content (Unit Of Measure)       | mg Protein     |
| Vial Content (Actual Content)        | ≥ 0.500        |
| Vial Content (Overpack)              | 1.00 - 40.00 % |
| Attachment (Attach./Toxicity)        | Pass           |
| Sterility                            | Pass           |
| Human Source (HbSAg)                 | Negative       |
| Human Source (HCV)                   | Negative       |
| Human Source (HIV)                   | Negative       |
| Human Source (HTLV)                  | Negative       |
| Recommended Retest Period<br>3 Years | -----          |

Specification: PRE.1.ZQ5.10000004364

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.