

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaldrich.com](http://www.sigmaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:

Sodium cyanoborohydride - reagent grade, 95%

**Product Number:****156159**

CAS Number:

25895-60-7

MDL:

MFCD00003516

Formula:

CH<sub>3</sub>BNNa

Formula Weight:

62.84 g/mol

NaBH<sub>3</sub>CN**TEST****Specification**

Appearance (Color)

White to Off-White

Appearance (Form)

Powder

Titration with Na<sub>2</sub>S<sub>2</sub>O<sub>3</sub>

94.5 - 105.5 %

Solubility (Color)

Colorless

Solubility Concentration: 100 mg/mL H<sub>2</sub>O

Solubility (Turbidity)

Clear to Hazy

Recommended Retest Period

2 Years

Specification: PRD.1.ZQ5.10000011879

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.