


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:
Ethyl cinnamate - natural, ≥95%, FG

Product Number: W243019
CAS Number: 103-36-6
MDL: MFCD00009189
Formula: C₁₁H₁₂O₂
Formula Weight: 176.21 g/mol



TEST	Specification
Appearance (Color)	Colorless to Faint Yellow
Appearance (Form)	Liquid
Refractive index at 20 ° C	1.557 - 1.561
Infrared spectrum	Conforms to Structure
Purity (GC)	≥ 95.0 %
Color test (APHA)	Results
300 APHA Maximum	
Organoleptics	Pass
Arsenic (As)	≤ 3 ppm
Cadmium (Cd)	≤ 1 ppm
Mercury (Hg)	≤ 1 ppm
Lead (Pb)	≤ 10 ppm
Expiration Date Period	-----
5 Years	

Specification: PRD.2.ZQ5.10000031841

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.