


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:
Benzyl bromide - reagent grade, 98%

Product Number: B17905
CAS Number: 100-39-0
MDL: MFCD00000172
Formula: C₇H₇Br
Formula Weight: 171.03 g/mol



TEST

Specification

Appearance (Color)	Colorless to Yellow
Appearance (Form)	Liquid
Infrared spectrum	Conforms to Structure
Color Test	≤ 400 APHA
Purity (GC)	≥ 97.5 %

Specification: PRD.0.ZQ5.10000017314

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.