

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaldrich.com

Email USA: techserv@sial.com

Outside USA: eurtechserv@sial.com


Product Specification

Product Name:
Ivermectin

Product Number: **I8898**

MDL: MFCD00869511

Storage Temperature: 2 - 8 °C



TEST	Specification
Appearance (Color)	White to Off-White
Appearance (Form)	Powder
Solubility (Color)	Colorless to Faint Yellow
Solubility (Turbidity)	Clear
50 mg/ml, Methyl Ethyl Ketone	
Water (by Karl Fischer)	≤ 1.0 %
Solvent Content (by GC)	≤ 5.0 %
EtOH	
Solvent Content (by GC)	≤ 3.0 %
Formamide	
Purity (HPLC)	≥ 90 %
Ivermectin B1A	
Isomer	≤ 5 %
Ivermectin B1B	
Recommended Retest Period	-----
3 years	

Specification: PRD.0.ZQ5.10000011510

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.