


Product Specification

Product Name :	Dihydrostreptomycin sesquisulfate BioReagent, suitable for cell culture, ≥95.0% (HPLC)
Product Number:	D5155
CAS Number:	5490-27-7
Storage Temperature :	Cooler/Refrigerated
Molecular Formula:	$C_{27}H_{41}N_7O_{12} \cdot 1.5H_2SO_4$
Formula Weight:	730.71



Test	Specification
Appearance (Form)	Powder
Appearance (Color)	White to Off-White
Loss on Drying	≤ 6.0%
Results Provided by Supplier	-----
Cell Culture Test	Pass
Tested by Releasing Site	-----
Shelf Life Defined by Supplier	-----
Handled & Packed Under ISO9001	-----
Released by	Expiration Date

Sigma-Aldrich warrants that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.

Version Number: PRP.02.ZQ5.1095838

Page 1 of 1

The branding on the header and/or footer of this document may temporarily not visually match the product purchased as we transition our branding. However, all of the information in the document regarding the product remains unchanged and matches the product ordered. For further information please contact mlsbranding@sial.com

