

3050 Spruce Street, Saint Louis, MO 63103, USA


Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:  
Isopropyl cinnamate -  $\geq 96\%$ , FG

Product Number: **W293903**

CAS Number: 7780-06-5



Formula: C<sub>12</sub>H<sub>14</sub>O<sub>2</sub>  
Formula Weight: 190.24 g/mol

TEST	Specification
------	---------------

Appearance (Color)	Colorless to Pale Yellow
Appearance (Form)	Liquid
Refractive index at 20 ° C	1.540 - 1.550
Infrared spectrum	Conforms to Structure
Purity (GC)	$\geq 96.0 \%$
Arsenic (As)	$\leq 3$ ppm
Cadmium (Cd)	$\leq 1$ ppm
Mercury (Hg)	$\leq 1$ ppm
Lead (Pb)	$\leq 10$ ppm
Expiration Date Period	-----
5 Years	

Specification: PRD.0.ZQ5.10000043775

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.