


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaldrich.com](http://www.sigmaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:  
(±)-3-Hydroxyoctanoic acid - ≥97%

**Product Number:** H3898  
**CAS Number:** 88930-08-9  
**MDL:** MFCD00133277  
**Formula:** C<sub>8</sub>H<sub>16</sub>O<sub>3</sub>  
**Formula Weight:** 160.21 g/mol  
**Storage Temperature:** -20 °C



TEST	Specification
Appearance (Color)	White to Off-White
Appearance (Form)	Powder or Solid
Solubility (Color)	Colorless to Faint Yellow
Solubility (Turbidity)	Clear
25mg/ml, EtOH	
Proton NMR spectra	Conforms to Structure
Purity (GC)	≥ 96.5 %

Specification: PRD.2.ZQ5.10000006976

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.