

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:

Diethyl azodicarboxylate solution - 40 wt. % in toluene

Product Number:

563110

MDL:

MFCD00009103

Formula:


C₆H₁₀N₂O₄

Formula Weight:

174.2 g/mol

Storage Temperature:

2 - 8 °C



TEST

Specification

Appearance (Color)

Orange

Appearance (Form)

Liquid

Infrared spectrum

Conforms to Structure

Proton NMR spectrum

Conforms to Structure

Proton NMR (Wt % Solution)

37.0 - 43.0 %

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.