


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:
Tetracaine - meets USP testing specifications

Product Number: T3812
CAS Number: 94-24-6
MDL: MFCD00053787
Formula: C₁₅H₂₄N₂O₂
Formula Weight: 264.36 g/mol
Storage Temperature: 2 - 8 °C



TEST	Specification
Identity	Pass
Loss on Drying	≤ 0.5 %
Residue on ignition (Ash)	≤ 0.1 %
Organic Impurities	Pass
Assay	98.0 - 102.0 %
dried basis	
Expiration Dated Product	-----
Residual Solvents	Meets Requirements

Specification: PRD.2.ZQ5.10000051248

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.