

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification


Product Name:  
Cyclopentylmagnesium bromide solution - 2.0 M in diethyl ether

Product Number: **428337**

MDL: MFCD00209569

Formula: C<sub>5</sub>H<sub>9</sub>BrMg

Formula Weight: 173.33 g/mol



### TEST

### Specification

Appearance (Clarity)

Clear to Slightly Hazy

Titration Sec-Butanol

1.90 - 2.20 M

Note

Note

This material can vary from light to very dark in appearance.

These differences in color will have no effect on use.

Specification: PRD.0.ZQ5.10000041667

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.