

3050 Spruce Street, Saint Louis, MO 63103, USA


Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:  
Hexyl propionate – natural (US), ≥97%, FG

Product Number: **W257615**

CAS Number: 2445-76-3



Formula: C<sub>9</sub>H<sub>18</sub>O<sub>2</sub>

Formula Weight: 158.24 g/mol

### TEST

### Specification

Appearance (Color)	Colorless
Appearance (Form)	Liquid
Refractive index at 20 ° C	1.410 - 1.416
Infrared spectrum	Conforms to Structure
Purity (GC)	≥ 97.0 %
Arsenic (As)	≤ 3 ppm
Cadmium (Cd)	≤ 1 ppm
Mercury (Hg)	≤ 1 ppm
Lead (Pb)	≤ 10 ppm
Expiration Date Period	-----
60 Months	

Specification: PRD.1.ZQ5.10000021320

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.