

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:

Fibronectin Proteolytic Fragment from human plasma - lyophilized powder, 45 kDa

Product Number:

F0162

TEST	Specification
Appearance (Form)	Lyophilized Powder
Appearance (Colour)	White
Solubility (Solvent)	Water
Solubility (Conc)	≥ 0.500 mg/ml
Solubility (Turbidity)	Clear to Slightly Hazy
Solubility (Color)	Colorless
Human Source (HbSAg)	Negative
Human Source (HCV)	Negative
Human Source (HIV)	Negative
Human Source (HTLV)	Negative
Protein Content (Method)	Lowry
Prot. Content (% Protein)	0.50 - 1.50 %
Gel Electroph. (Gel)	SDS-Page
Gel Electroph. (Stain)	Coomassie
Gel Elec. (Maj. Band at kDa)	45 - 45 kDa
Gel Electroph. (Purity)	≥ 90.0 %
Vial Content (Size)	0.500 - 0.500
Vial Content (Unit Of Measure)	mg Protein
Vial Content (Actual Content)	≥ 0.500
Vial Content (Overpack)	1.00 - 30.00 %
Recommended Retest Period	-----
3 Years	

Specification: PRE.1.ZQ5.10000002763

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.