

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaldrich.com](http://www.sigmaldrich.com)


Email USA: [techserv@sial.com](mailto:techserv@sial.com)

Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:  
Meperidine hydrochloride

**Product Number:** M3142  
**CAS Number:** 50-13-5  
**MDL:** MFCD00058210  
**Formula:** C<sub>15</sub>H<sub>21</sub>NO<sub>2</sub> · HCl  
**Formula Weight:** 283.79 g/mol



### TEST

### Specification

Appearance (Color)	White
Appearance (Form)	Powder
Solubility (Color)	Colorless
Solubility (Turbidity)	Clear
50 mg/ml in H <sub>2</sub> O	
Infrared spectrum	Conforms to Structure
Carbon	62.2 - 64.8 %
Nitrogen	4.6 - 5.2 %
Purity (GC)	≥ 99 %
Recommended Retest Period	-----
4 years	

Specification: PRD.0.ZQ5.10000033382

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.