

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:

Protein Kinase C ζ isozyme human - $\geq 75\%$ (SDS-PAGE), recombinant, expressed in baculovirus infected insect cells, buffered aqueous solution

Product Number:

P0194



MDL:

MFCD03458228

Storage Temperature:

-70 °C

TEST	Specification
------	---------------

mg protein/ml (Bradford)

 ≥ 0.1

Enzymatic Activity

 ≥ 800 UN/mg

units/mg protein

Unit definition: One unit will transfer 1 nanomole of phosphate to PKC epsilon substrate peptide per minute at pH 7.5 at 30 deg C.

Purity by SDS Electrophoresis

Conforms

> or = 75%

Specification: PRD.0.ZQ5.10000057235

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.