

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)


Email USA: [techserv@sial.com](mailto:techserv@sial.com)

Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:  
6-Methylcoumarin - ≥99%, FCC, FG

**Product Number:** W269905  
**CAS Number:** 92-48-8  
**MDL:** MFCD00006875  
**Formula:** C10H8O2  
**Formula Weight:** 160.17 g/mol



TEST	Specification
Appearance (Color)	White
Appearance (Form)	Powder or Solid or Crystals
Melting Point	73 - 76 °C
Infrared spectrum	Conforms to Structure
Purity (GC)	≥ 99.00 %
Solubility (Turbidity)	Clear to Slightly Hazy
1g/20ml 95% Ehtanol	
Solubility (Color)	Colorless to Pale Yellow
Arsenic (As)	≤ 3 ppm
Cadmium (Cd)	≤ 1 ppm
Mercury (Hg)	≤ 1 ppm
Lead (Pb)	≤ 10 ppm
Expiration Date Period	-----
5 Years	

Specification: PRD.1.ZQ5.10000011588

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.