

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:

Anti-Myosin VI (KA-15) antibody produced in rabbit - affinity isolated antibody, buffered aqueous solution

Product Number:

M5187

Storage Temperature:

-20 °C

| TEST | Specification |
|------------------------------|------------------------|
| Appearance (Form) | Liquid |
| Appearance (Turbidity) | Clear to Slightly Hazy |
| Appearance (Color) | Colorless |
| IgG Concentration (OD 280nm) | 1.0 - 1.5 mg/ml |
| WB-Cell Line/Tissue Extract | MDCK |
| WB Titer | 1:1000-1:2000 |
| ICC/IF Cells | NRK rat kidney cells |
| ICC/IF Fixation Reagent 1 | 3%-4% Paraformaldehyde |
| ICC/IF-Fixation Reagent 2 | 0.2% Triton X-100 |
| ICC/IF-Titer | 1:75-1:150 |
| Recommended Retest Period | ----- |
| 4 Years | |

Specification: PRE.0.ZQ5.10000017426

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.