

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.com

Email USA: techserv@sial.com


Outside USA: eurtechserv@sial.com

Product Specification

Product Name:

1,2-Dihexanoyl-sn-glycero-3-phosphocholine - solution, 20 mg/mL in chloroform, ≥99%

Product Number: P4148
CAS Number: 34506-67-7
MDL: MFCD00050431
Formula: C₂₀H₄₀NO₈P
Formula Weight: 453.51 g/mol
Storage Temperature: -20 °C



TEST

Specification

Appearance (Color)	Colorless
Appearance (Form)	Liquid
Appearance (Turbidity)	Clear
Solid Content	17.5 - 22.5 mg/ml
Proton NMR spectrum	Conforms to Structure
Purity (TLC)	≥ 99 %
Purity (GC)	≥ 99 %
as Caproic Acid	

Specification: PRD.0.ZQ5.10000019594

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.