

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.com


Email USA: techserv@sial.com

Outside USA: eurtechserv@sial.com

Product Specification

Product Name:
Docusate sodium – meets USP testing specifications

Product Number: **D1685**
 CAS Number: 577-11-7
 MDL: MFCD00012455
 Formula: C₂₀H₃₇NaO₇S
 Formula Weight: 444.56 g/mol



TEST	Specification
Water (by Karl Fischer)	≤ 2.0 %
Residue on ignition (Ash)	15.5 - 16.5 %
Anhydrous basis	
Bis(2-ethylhexyl) maleate	≤ 0.4
Limit of	
Assay	99.0 - 100.5 %
anhydrous basis	
Residual Solvents	Meets Requirements
Identity	Pass
Clarity of Solution	Pass
Recommended Retest Period	-----
2 Years	

Specification: PRD.3.ZQ5.10000042985

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.