

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:

Anti-Histone Deacetylase 3 (HDAC3) antibody produced in rabbit - IgG fraction of antiserum, buffered aqueous solution

Product Number:

H3034

Storage Temperature:

-20 #C

**TEST****Specification**

Appearance (Form)	Liquid
Appearance (Turbidity)	Clear to Slightly Hazy
Appearance (Color)	Colorless
IgG Concentration (OD 280nm)	9.0 - 15.0 mg/ml
WB-Cell Line/Tissue Extract	Hela Cells Nuclear Fr.
WB Titer	1:10,000-1:20,000
WB-Cell Line/Tissue Extract	PC-12 cells
WB-Titer	1:2000-1:4000
IP - Cell /Tissue Lysate	NIH-3T3 Mouse Fibroblasts
IP - Antibody Precipitation	5 - 10 UL
IHC - Tissue	Human Lymph Node
IHC - Fixation	FFPE-Formalin Fixed Paraffin Embedded
IHC - Titer	1:500-1:1000
Recommended Retest Period	-----
4 Years	

Specification: PRE.0.ZQ5.10000020680

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.