

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:  
SigmaMarker™ - High Range, mol wt 36,000-200,000 Da

Product Number: **S8320**

MDL: MFCD00165844

TEST	Specification
------	---------------

Appearance (Color)	Blue
Appearance (Form)	Lyophilized Powder
Suitability	Suitable
by SDS-PAGE: Seven well defined major bands of approximately equal intensity at the following molecular weights (in Daltons): Myosin, Porcine Heart: 200,000	
Beta-Galactosidase, E.coli: 116,000	
Phosphorylase B, Rabbit Muscle: 97,000	
Albumin, Bovine Serum: 66,000	
Glutamic Dehydrogenase, Bovine Liver: 55,000	
Ovalbumin, Chicken Egg: 45,000	
Glyceraldehyde-3-Phosphate Dehydrogenase, Rabbit Muscle: 36,000	

Specification: PRD.0.ZQ5.10000012722

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.