

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:

Monoclonal Anti-Fibronectin, Cellular antibody produced in mouse - clone FN-3E2, ascites fluid

Product Number:

F6140

Storage Temperature:

-20 °C

**TEST****Specification**

Appearance (Form)	Liquid
Appearance (Turbidity)	Clear to Slightly Hazy
Appearance (Color)	Very Faint Yellow to Very Dark Yellow to Very Dark Brown
Protein by Biuret	15 - 55 mg/ml
Mouse IgM by RID	0.8 - 2.0 mg/ml
WB-Cell Line/Tissue Extract	Chicken Fibroblast
WB Titer	1:1000-1:2000
ICC/IF Cells	Chicken Fibroblast
ICC/IF Fixation Reagent 1	3%-4% Paraformaldehyde
ICC/IF-Fixation Reagent 2	0.5% Triton X-100
ICC/IF-Titer	1:400-1:800
Recommended Retest Period	-----
5 Years	

Specification: PRE.0.ZQ5.10000018674

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.