


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:
Poly-L-arginine hydrochloride - mol wt >70,000

Product Number: **P3892**
CAS Number: 26982-20-7
MDL: MFCD00166393



Storage Temperature: -20 °C

TEST	Specification
Appearance (Color)	White to Off-White
Appearance (Form)	Powder or Solid
Solubility (Color)	Colorless to Faint Yellow
Solubility (Turbidity)	Clear to Slightly Hazy
50 mg/ml H ₂ O	
Water (by Karl Fischer)	≤ 10 %
Degree of Polymerization	> 363
by viscosity	
Molecular weight	> 70000
by viscosity	
TLC	Conforms
< or = 3% ornithine	

Specification: PRD.2.ZQ5.10000009975

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.