

3050 Spruce Street, Saint Louis, MO 63103, USA


Website: www.sigmaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:
Isopropylmagnesium chloride solution - 2.0 M in THF

Product Number: **230111**

MDL: MFCD00000466
Formula: C₃H₇ClMg
Formula Weight: 102.85 g/mol



TEST	Specification
------	---------------

Appearance (Clarity)	Clear
Titration w/ 2-Butanol	1.80 - 2.20 M
Note	Note
#1 - Haziness may form upon storage but does not affect specification.	
#2 - If precipitation is present, then gently mix precipitate back into solution under an inert atmosphere.	
#3 - This material can vary from light to very dark in appearance. These differences in color will have no effect on use.	

Specification: PRD.3.ZQ5.10000014176

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.