

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaldrich.com](http://www.sigmaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:

Anti-Chicken IgY (IgG) (whole molecule) antibody produced in rabbit - affinity isolated antibody, buffered aqueous solution

Product Number:

**C2288**

Storage Temperature:

-20 °C

TEST	Specification
Appearance (Form)	Liquid
Appearance (Turbidity)	Clear
Appearance (Color)	Colorless
IgG Concentration (OD 280nm)	2.0 - 2.5 mg/ml
ELISA - Titer	1:25,000-1:50,000
Recommended Retest Period	-----
4 Years	

Specification: PRE.0.ZQ5.10000020960

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.