

3050 Spruce Street, Saint Louis, MO 63103, USA


Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:
DL-Aspartic acid – Vetec™ reagent grade

Product Number: **V900720**
CAS Number: 617-45-8

Formula: C₄H₇NO₄
Formula Weight: 133.1 g/mol



TEST	Specification
Appearance (Colour)	White
Appearance (Form)	Powder
Solubility (Colour)	Colorless
Solubility (Turbidity)	Clear
50 mg/ml, 1 M HCl	
Infrared spectrum	Conforms to Structure
Specific Rotation	-0.49 - 0.49 deg
c = 2 in 1 M HCl at 25 deg C	
Purity (TLC)	≥ 98.0 %

Specification: PRE.0.ZQ5.10000002522

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.