

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaldrich.com](http://www.sigmaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)**Product Specification**

Product Name:

Hexacosanoic acid ≥95% (capillary GC)

**Product Number:****H0388**

CAS Number:

506-46-7

MDL:

MFCD00002811

Formula:


C<sub>26</sub>H<sub>52</sub>O<sub>2</sub>

Formula Weight:

396.69 g/mol

Storage Temperature:

2 - 8 °C



<b>TEST</b>	<b>Specification</b>
Appearance (Color)	White to Off-White
Appearance (Form)	Powder
Solubility (Color)	Colorless to Faint Yellow
Solubility (Turbidity) at 50 mg/mL in Chloroform	Clear
Purity (GC)	≥95 %
Recommended Retest Period 5 years	-----

**Remarks:**

Specification Date : 01/19/2011

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.