

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:
Dinonylnaphthalenedisulfonic acid solution - 55 wt. % in isobutanol


Product Number: **522988**

MDL: MFCD02094639

Formula: C₂₈H₄₄O₆S₂

Formula Weight: 540.78 g/mol

Storage Temperature: 2 - 8 °C



TEST

Specification

| | |
|-------------------------|-----------------------|
| Appearance (Color) | Colorless to Brown |
| Appearance (Form) | Liquid |
| Infrared spectrum | Conforms to Structure |
| Water (by Karl Fischer) | ≤ 4.0 % |
| Miscellaneous Assay | 54.0 - 56.0 % |
| Actives | |
| Acid Value | 112.0 - 116.0 |

Specification: PRD.0.ZQ5.10000039160

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.