

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)


Email USA: [techserv@sial.com](mailto:techserv@sial.com)

Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:  
Styrene - ReagentPlus®, contains 4-tert-butylcatechol as stabilizer, ≥99%

**Product Number:** S4972  
**CAS Number:** 100-42-5  
**MDL:** MFCD00008612  
**Formula:** C<sub>8</sub>H<sub>8</sub>  
**Formula Weight:** 104.15 g/mol  
**Storage Temperature:** 2 - 8 °C



TEST	Specification
------	---------------

Appearance (Color)	Colorless
Appearance (Form)	Liquid
Infrared spectrum	Conforms to Structure
Purity (GC)	≥ 99.0 %
Turbidity	≤ 3.5 NTU
Color Test	≤ 20 APHA
Note	-----
Inhibitor depletes over time especially at higher temperatures. 50 ppm of 4-tert-butylcatechol is added as stabilizer when packaged.	
Recommended Retest Period	-----
1 Year	

Specification: PRD.0.ZQ5.10000024112

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.