


Product Specification

Product Name:
Indoxyl acetate - $\geq 95\%$ (GC)

Product Number: **I3500**
CAS Number: 608-08-2
Formula: C₁₀H₉NO₂
Formula Weight: 175.19 AMU



TEST	Specification
------	---------------

Appearance (Colour)	Conforms to Requirements
Appearance (Form)	Powder
Purity (GC)	$\geq 95.0\%$
Solubility (Colour)	Colorless to Light Yellow and Very Faint Brown to Light Brown and Very Faint Pink to Light Pink and Very Faint Purple to Light Purple
Solubility (Turbidity)	Clear to Slightly Hazy
Carbon Content	66.0 - 70.0 %
Nitrogen Content	7.5 - 8.5 %
Infrared Spectrum	Conforms to Structure

Specification: PRE.2.ZQ5.10000020549

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.

