


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:
Nervonic acid - ≥99% (capillary GC)

Product Number: N1514
CAS Number: 506-37-6
MDL: MFCD00010507
Formula: C₂₄H₄₆O₂
Formula Weight: 366.62 g/mol
Storage Temperature: -20 °C



TEST	Specification
Appearance (Color)	White
Appearance (Form)	Powder
Proton NMR spectrum	Conforms to Structure
Solubility (Color)	Colorless
Solubility (Turbidity) 50 mg/mL, CHCl ₃	Clear
Purity (GC)	≥ 99 %

Specification: PRD.0.ZQ5.10000044554

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.