


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:
MOPSO - ≥99% (titration)

Product Number: M8389
CAS Number: 68399-77-9
MDL: MFCD00009629
Formula: C7H15NO5S
Formula Weight: 225.26 g/mol



TEST	Specification
Appearance (Color)	White
Appearance (Form)	Crystalline Powder
Solubility (Color)	Colorless
Solubility (Turbidity)	Clear
10 g plus 30 ml of H2O	
Water (by Karl Fischer)	≤ 0.5 %
A290 UV absorbance	≤ 0.1
25% W/W	
Heavy Metals (as Lead)	< = 5 ppm
Purity (Titr. by NaOH) anhyd.	≥ 99 %
Recommended Retest Period	-----
3 years	
Infrared spectrum	Conforms to Structure

Specification: PRD.1.ZQ5.10000043685

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.