


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:  
Mercaptosuccinic acid – Vetec™ reagent grade

Product Number: **V900745**  
CAS Number: 70-49-5  
Formula: C<sub>4</sub>H<sub>6</sub>O<sub>4</sub>S  
Formula Weight: 150.15 g/mol



TEST	Specification
Appearance (Colour)	White
Appearance (Form)	Powder
Solubility (Turbidity) c = 50mg/ml, H <sub>2</sub> O	Clear to Slightly Hazy
Solubility (Colour)	Colorless to Faint Yellow
Infrared spectrum	Conforms to Structure
Purity (Titration by NaOH)	96.5 - 103.5 %

Specification: PRE.0.ZQ5.10000002515

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.