

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification


Product Name:
DABCYL SE - solidProduct Number: **D9689**

MDL: MFCD00467415

Formula: C₁₉H₁₈N₄O₄

Formula Weight: 366.37 g/mol

Storage Temperature: -20 °C



TEST	Specification
Appearance (Color)	Orange to Red
Appearance (Form)	Solid
Proton NMR spectrum	Conforms to Structure
EmM	31.0 - 36.0
Lambda Max of 450 to 456 nm, MeOH	
Wavelength	450 - 456 nm
Purity (HPLC)	≥ 90 %

Specification: PRD.0.ZQ5.10000035867

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.