


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:
Urea hydrogen peroxide - 97%

Product Number: 289132
CAS Number: 124-43-6
MDL: MFCD00013119
Formula: CH₄N₂O · H₂O₂
Formula Weight: 94.07 g/mol
Storage Temperature: 2 - 8 °C



TEST	Specification
Appearance (Color)	White
Appearance (Form)	Powder or Crystals
Infrared spectrum	Conforms to Structure
Assay Redox Titration	96.5 - 103.5 %
Solubility (Turbidity) c = 50mg/ml (5%), H ₂ O	Clear
Solubility (Color)	Colorless

Specification: PRD.1.ZQ5.10000004393

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.