


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:  
Methyl 4-hydroxybenzoate - ReagentPlus®, ≥99.0%, crystalline

Product Number: **H5501**  
CAS Number: 99-76-3  
MDL: MFCD00002352  
Formula: C<sub>8</sub>H<sub>8</sub>O<sub>3</sub>  
Formula Weight: 152.15 g/mol



TEST	Specification
Appearance (Color)	Colorless or White
Appearance (Form)	Powder or Crystals
Solubility (Color)	Colorless
Solubility (Turbidity)	Clear
50 mg/mL, EtOH	
<sup>1</sup> H NMR Spectrum	Conforms to Structure
Residue on ignition (Ash)	≤ 0.1 %
Loss on Drying	≤ 0.3 %
Purity (HPLC)	≥ 99.0 %
Recommended Retest Period	-----
5 Years	

Specification: PRD.4.ZQ5.10000041940

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.