

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:

Anti-Munc-18-1 antibody produced in rabbit - IgG fraction of antiserum, buffered aqueous solution

Product Number:

M2694

Storage Temperature:

-20 °C

TEST**Specification**

Appearance (Form)	Liquid
Appearance (Turbidity)	Clear to Slightly Hazy
Appearance (Color)	Colorless
IgG Concentration (OD 280nm)	5.0 - 10.0 mg/ml
WB-Cell Line/Tissue Extract	Rat Brain S1 Frac.
WB-Western Blot Titer	1:2000-1:4000
WB-Cell Line/Tissue Extract	PC-12 cells
WB-Western Blot Titer	1:2000-1:4000
ICC/IF Cells	NIH-3T3 Mouse Fibroblasts
ICC/IF Fixation Reagent 1	Methanol
ICC/IF-Fixation Reagent 2	Acetone
ICC/IF-Titer	1:250-1:500
Recommended Retest Period	-----
4 Years	

Specification: PRE.0.ZQ5.10000018205

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.