

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaldrich.com](http://www.sigmaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:

Anti-Actin (20-33) antibody produced in rabbit - IgG fraction of antiserum, buffered aqueous solution

Product Number:

A5060

Storage Temperature:

-20 °C

**TEST****Specification**

Appearance (Form)	Liquid
Appearance (Turbidity)	Clear
Appearance (Color)	Colorless
IgG Concentration (OD 280nm)	10.0 - 20.0 mg/ml
WB-Cell Line/Tissue Extract	Chicken gizzard or Rat brain
WB Titer	1:250-1:500
ICC/IF Cells	Chicken Fibroblast
ICC/IF Fixation Reagent 1	3%-4% Paraformaldehyde
ICC/IF-Fixation Reagent 2	Cold (-20°C) Methanol
ICC/IF-Titer	1:200-1:400
IHC - Tissue	Chicken intestine or Rat tongue
IHC - Fixation	FFPE-Formalin Fixed Paraffin Embedded
IHC - Titer	1:100-1:200
Recommended Retest Period	-----
4 Years	

Specification: PRE.0.ZQ5.10000013918

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.