

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:

Anti-Fibronectin antibody produced in rabbit – affinity isolated antibody, buffered aqueous solution

Product Number:

F3648

TEST	Specification
------	---------------

Appearance (Form)	Liquid
Appearance (Turbidity)	Clear
Appearance (Color)	Colorless
IgG Concentration (OD 280nm)	0.5 - 0.7 mg/ml
ELISA - Titer	1:10,000-1:20,000
WB-Cell Line/Tissue Extract	Fibronectin from human plasma
WB Titer	1:1000-1:2000
Dot Blot-Titer	1:2000-1:4000
ICC/IF Cells	HS-68 Human Foreskin Fibroblasts Cells
ICC/IF Fixation Reagent 1	3%-4% Paraformaldehyde
ICC/IF-Fixation Reagent 2	0.5% Triton X-100
ICC/IF-Titer	1:400-1:800
Recommended Retest Period	-----
4 Years	

Specification: PRE.0.ZQ5.10000016054

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.